

Certified GRCop-42 (A)

Certified GRCop-42 (A) is a copper alloy specifically designed for hightemperature, high-thermal transfer applications where high strength and creep properties are also a hard requirement. Parts in GRCop-42 can operate reliably up to a service temperature of approximately 750 °C.

3D Systems offers application development and part production using the integrated additive manufacturing (AM) workflow software, 3DXpert[®], and the DMP Flex and DMP Factory 350 metal 3D printers. 3D Systems' Certified GRCop-42 parameters were developed, tested, and optimized on real heat management applications in cooperation with our AS9100/ ISO9001 part production facilities, which have the unique distinction of printing more than 1,000,000 challenging metal production parts in various materials, year over year.

For companies looking to develop new applications and processes with Certified GRCop-42, our Application Innovation Group (AIG) can support and accelerate application development.

Typical Properties

DMP FLEX 350, DMP FACTORY 350 - LT 60 ²	TEST METHOD	HEAT TREATMENT HIP ³
Ultimate tensile strength (MPa ksi)	ASTM E8	360 52
Yield strength Rp0.2% (MPa ksi)		195 28
Elongation (%)		33
Electrical conductivity (% IACS1)	ASTM B193	>85

Typical Applications

- Regeneratively cooled, liquid bi-propellant thrust chambers
- High-temperature aerospace components
- Advanced thermal management with high conductivity needs in temperatures up to 800°C
- High thermal transfer applications where pure Cu is too weak

Material Description

Certified GRCop-42 is a copper-chrome-niobium alloy developed by NASA. The addition of Cr and Nb to the Cu matrix enables dispersion strengthening after HIP via Cr2Nb precipitates. These precipitates improve mechanical strength, creep resistance and low cycle fatigue life at high temperatures. At room temperature, electrical conductivity of over 85% IACS1 can be obtained.

Certified GRCop-42 (A) powder chemistry

ELEMENT	WT%
Cr	3.1 - 3.4
Nb	2.7 - 3.0
Fe	< 250 ppm, target < 50 ppm
0	< 500 ppm, target < 250 ppm
Al	< 400 ppm
Si	< 350 ppm, target < 100 ppm
Cu	Balance

Source: NASA report AIAA-2019-4228

3D Systems offers this standard alloy now as a solution for additive manufacturing. The extremely low oxygen environment of the DMP Flex and Factory 350 vacuum chamber azrchitecture minimizes oxygen pickup, ensuring the best conductivity properties. And with the DMP Factory 350 system, the powder handling can be done completely in an inert environment.



- Samples printed with a layer thickness of 60 µm (LT60). Machined and tested according to ASTM E8 using round tensile test specimen type 4. Typical values, average of 10 vertical and 23 horizontal tensile coupons. HIP = Hot Isostatic Pressing 954°C for 3 hours at 103Mpa

IACS = International Annealed Copper Standard.

Layer thickness 60 relative density typically 99.8 - 99.9%4 after HIP



Application Focus:

SPACE - THRUST CHAMBERS

The high thermal conductivity of GRCop-42 greatly improves cooling of the chamber during operation. As a result, GRCop-42 allows combustion chambers to operate at higher temperatures which significantly increases efficiency. Moreover, GRCop-42 is an alloy specifically designed to meet the strength and creep requirements desired by the space industry. With a service temperature up to 750°C, GRCop-42 is therefore a go-to material for use in load-bearing hightemperature (typically 400-600°C) propulsion applications.

JUGGLE COMPLEXITY AND SIMPLIFY ASSEMBLY IN 3DXPERT

Benefit from the 3DXpert design features to generate cooling channels with unlimited complexity. Analyze your design inside the same software environment. Leverage the power of additive manufacturing to simplify assemblies by integrating additional functions such as structural elements and fixtures into a single part.

8 - 10 μm	
	C.
	, en
Typical Electrical Conductivity > 85% IACS ¹	
	A MINING
	-
2	A A A A A A A A A A A A A A A A A A A

Typical Roughness Ra

Part height	260 mm
Print time	45 h (Batch size: 1)
Layer thickness	60 µm

4. Values based on a limited sample population (<15). Values shown are typical values from density test coupons, may deviate depending on specific part geometry. No surface treatment applied, measured in as printed condition according with a Keyence microscope. Values based on a limited sample population (<5)

🙏 3D SYSTEMS

To confirm the suitability of this material for your specific application, please contact the 3D Systems Application Innovation Group (AIG): https://www.3dsystems.com/consulting/application-innovation-group

CERTIFIED GRCOP-42 (A) | MATERIAL DATASHEET | 3DS-10127A | 07-23

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

©2023 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo and 3DXpert are registered trademarks of 3D Systems, Inc.

