



Accura[®] AMX[™] High Temp 300C

High Temperature

Ultra-high temperature resistant rigid plastic engineered to withstand the harshest thermal environments

Stereolithography

HIGH THERMAL RESISTANCE, TRANSLUCENT PLASTIC FOR ELEVATED TEMPERATURE FLUID OR FLOW VISUALIZATION

Accura AMX High Temp 300C is an ultra-high temperature stereolithography resin that is engineered to meet the demands of applications requiring the highest levels of heat resistance. It is the industry's most heat resistant stereolithography (SLA) material with a heat deflection temperature (HDT) of over 300 °C at low stress (at 0.455 MPa) that does not require a post thermal cure.

This material is well suited for the testing of high temperature components in applications including HVAC, consumer appliances, motor enclosures, fixtures, mounts, stators, molding/tooling, among many others.



APPLICATIONS

- High temperature components testing, and general use parts including: HVAC, consumer appliances, motor enclosures, stators, etc.
- Low pressure molding/tooling: expanding foams, rubbers, etc.
- Functional prototype and production components for fixtures, mounts, housings, white goods and personal care products
- Elevated temperature fluid or gas flow visualization
- Overmolding

BENEFITS

- Production-grade material
- High heat resistant for testing and use in high heat environments
- Shortened production workflow; no requirement for a post thermal cure
- Excellent visualization for parts requiring evaluation of internal features and fluid flow performance
- Chemical and auto fluid compatibility

MATERIAL PROPERTIES

The full suite of mechanical properties is given per ASTM and ISO standards where applicable. All parts are conditioned per ASTM recommended standards for a minimum of 40 hrs at 23°C, 50% RH. Solid material properties reported were printed along the vertical axis (ZX-orientation).

As detailed in the Isotropic Properties section, stereolithography material properties are relatively uniform across print orientations. Parts do not need to be oriented in a particular direction to exhibit these properties.

LIQUID MATERIAL			
METRIC	METHOD	METRIC	US
Viscosity (@25C)	Brookfield viscometer	1100 cPs	2661 lb/ft-h
Color		Amber	
Liquid Density (@25C)	Kruss K11 Force Tensiometer	1.17 g/cm ³	0.04 lb/in ³

SOLID MATERIAL						
METRIC	ASTM METHOD	METRIC	US	ISO METHOD	METRIC	US
PHYSICAL				PHYSICAL		
Solid Density	ASTM D792	1.27 g/cm ³	0.046 lb/in ³	ISO 1183	1.27 g/cm ³	0.046 lb/in ³
24 Hour Water Absorption	ASTM D570	0.36 %	0.36 %	ISO 62	0.36 %	0.36 %
MECHANICAL				MECHANICAL		
Tensile Strength Ultimate	ASTM D638 Type IV	59 MPa	8600 psi	ISO 527 -1/2	53 MPa	7700 psi
Tensile Strength at Yield	ASTM D638 Type IV	Did not yield	Did not yield	ISO 527 -1/2	Did not yield	Did not yield
Tensile Modulus	ASTM D638 Type IV	3500 MPa	500 ksi	ISO 527 -1/2	3500 MPa	500 ksi
Elongation at Break	ASTM D638 Type IV	2.2 %	2.2 %	ISO 527 -1/2	2.6 %	2.6 %
Elongation at Yield	ASTM D638 Type IV	Did not yield	Did not yield	ISO 527 -1/2	Did not yield	Did not yield
Flex Strength	ASTM D790	117 MPa	16900 psi	ISO 178	108 MPa	15700 psi
Flex Modulus	ASTM D790	3400 MPa	500 ksi	ISO 178	3600 MPa	528 ksi
Izod Notched Impact	ASTM D256	10 J/m	0.2 ft-lb/in	ISO 180-A	1.6 J/m ²	0.75 ft-lb/in ²
Izod Unnotched impact	ASTM D4812	70 J/m	1.3 ft-lb/in	ISO 180-U	6 J/m ²	2.96 ft-lb/in ²
Shore Hardness	ASTM D2240	88 D	88 D	ISO 7619	88 D	88 D
THERMAL				THERMAL		
Tg (DMA E'')	ASTM E1640 (E''Peak)	23 C	74 F	ISO 6721-1/11 (E'' Peak)	23 C	74 F
HDT 0.455MPa/66PSI	ASTM D648	300 C	572 F	ISO 75-1/2 B	300 C	572 F
HDT 1.82MPa/264 PSI	ASTM D648	124 C	255 F	ISO 75-1/2 A	115 C	238 F
CTE -20 TO 50C	ASTM E831	74 ppm/C	41 ppm/F	ISO 11359-2	74 ppm/C	41 ppm/F
CTE 75 TO 180C	ASTM E831	55 ppm/C	31 ppm/F	ISO 11359-2	55 ppm/C	31 ppm/F

ISOTROPIC PROPERTIES

Stereolithography technology prints parts that are generally isotropic in mechanical properties meaning the parts printed along either the XYZ axis will give similar results.

Parts do not need to be oriented to get the highest mechanical properties, further improving the degree of freedom for part orientation for mechanical properties.

SOLID MATERIAL						
METRIC	METHOD	METRIC				
MECHANICAL						
		ZX	XZ45	YX	Z45	XZ
Tensile Strength Ultimate	ASTM D638 Type IV	59 MPa	41 MPa	53 MPa	57 MPa	40 MPa
Tensile Strength at Yield	ASTM D638 Type IV	Did not yield	Did not yield	Did not yield	Did not yield	Did not yield
Tensile Modulus	ASTM D638 Type IV	3500 MPa	3500 MPa	3700 MPa	3500 MPa	3600 MPa
Elongation at Break	ASTM D638 Type IV	2.2 %	1.3 %	1.7 %	1.9 %	1.2 %
Flex Strength	ASTM D790	117 MPa	116 MPa	100 MPa	92 MPa	117 MPa
Flex Modulus	ASTM D790	3400 MPa	3500 MPa	2860 MPa	3200 MPa	3400 MPa
Izod Notched Impact	ASTM D256	10 J/m	10 J/m	10 J/m	10 J/m	10 J/m
Izod Unnotched Impact	ASTM D4812	70 J/m	67 J/m	56 J/m	65 J/m	73 J/m
HDT 0.455MPa/66PSI	ASTM D648	300 C	300 C	300 C	300 C	300 C
HDT 1.82MPa/264 PSI	ASTM D648	124 C	136 C	136 C	141 C	153 C

